High Accuracy

For Harsh Environment



Consistent Accuracy

Vibration, wind and temperature variances are outside influences that can cause errors in your formulations or mistakes in counting. The PFK9 Weighing Platforms virtually eliminate those risks, thanks to the Monobloc load cell and the robust design of the scale body, which absorbs environmental interference.



Smart Load-Cell Technology

The load cell, with Monobloc technology, is at the core of the PFK9 Weighing Platforms and guarantees the highest precision and reliability. A robust load – cell housing features integrated overload protection and durable mechanical interfaces. This ensures stable weight values for many years of intensive use.





Functional Design

Installing floor scales in pits is beneficial to allow easy loading and unloading of material on the ground level. The pit frames, which are available as an accessory for all floor scales, ensure short installation time and easy positioning and leveling.



Hazardous Environments

When working in a hazardous environment, safety is key. The PFK9 Weighing Platforms are approved for the use in hazardous areas for Category 3 / Division 2 and Category 2 / Division 1 for top performance in gaseous and dusty environments.

PFK9 Floor Platforms

Accurate - Reliable - Robust - Versatile

Accurate weighing helps you manage raw materials, ensure compliance with regulations and improve your product quality. For floor scale applications that require reliability with the best accuracy available, the PFK9 Weighing Platforms provide industry-leading performance. The wide range of platforms with four capacities from 300 to 3000 kilograms in four different sizes makes it suitable for a variety of applications and industries. The PFK9 Weighing Platforms can be connected to numerous METTLER TOLEDO terminals resulting in top-class weighing systems with benefits such as

- 30 000e resolution in legal-for-trade applications
- Up to 750 000d resolution for non-approved applications
- For safe as well as hazardous areas Category 3 / Division 2 and Category 2 / Division 1
- IP66/IP68 Ingress Protection
- Easy maintenance with built-in calibration weight



High Precision Floor Platforms Model Specific Data











									_
Models			C		D		E	E	S
	unit	C300	C600	D600	D1500	E1500	E3000	ES1500	ES3000
Maximum Capacity	[kg]	300	600	600	1500	1500	3000	1500	3000
Readability									
Accuracy Class II Single Range									
30 000e*	[g]	10*	20*	20*	50*	50*	100*	50*	100*
15 000e / 12 000e	[g]	20	50	50	100	100	200	100	200
7 500e / 6 000e	[g]	50	100	100	200	200	500	200	500
Accuracy Class III 3x10000e Multi Interval									
Max1 / e1	[kg/g]	100/10	200/20	200/20	500/50	500/50	1000/100	500/50	1000/100
Max2 / e2	[kg/g]	200/20	500/50	500/50	1000/100	1000/100	2000/200	1000/100	2000/200
Max3 / e3	[kg/g]	300/50	600/100	600/100	1500/200	1500/200	3000/500	1500/200	3000/500
Recommended Readability (min.) Single Range			•						
750 000d / 600 000d	[g]	0.5	1	1	2	2	5	2	5
300 000d / 240 000d	[g]	1	2	2	5	5	10	5	10
75 000d / 60 000d	[g]	5	10	10	20	20	50	20	50
Maximum Permissable Error at maximum load (Limit Values, approved platforms only)									
Class II, Single Range, 30 000e	[g]	15	30	30	75	75	150	75	150
Class III, Multi Interval, 3x10 000e	[g]	75	150	150	300	300	750	300	750
Minimum Capacities (approved platforms only)									•
Class II, Single Range, 30 000e	[kg]	0.05	1	1	2.5	2.5	0.5	2.5	0.5
Class II, Single Range, 15 000e /12 000e	[kg]	1	2.5	2.5	0.5	0.5	10	0.5	10
Class II, Single Range, 7 500e / 6 000e	[kg]	2.5	0.5	0.5	10	10	25	10	25
Class III, Multi Interval, 3x10 000e	[kg]	0.2	0.4	0.4	1	1	2	1	2
Zero-setting and Preload Range								•	•
Zero-setting range	[kg ±]	6	12	12	30	30	60	30	60
Preload range	[kg]	54	108	108	270	270	540	270	540
Maximum Static Safe Load			•		,				•
Central load	[kg]	1000	1000	3500	3500	4500	4500	4500	4500
Side load	[kg]	650	650	2300	2300	3000	3000	3000	3000
Corner load	[kg]	330	330	1150	1150	1500	1500	1500	1500
Typical Values**									
Repeatability sd (at max. load)	[g]	0.6	1.2	2.5	4	5	10	5	10
Error of Indication typ. (at half load)	[g]	2.5	5	8	16	20	40	20	40
Error of Indication typ. (at full load)	[g]	3	7	10	20	25	50	25	50
Eccentric load deviation typ (at 1/3 of max. load in t	he middle o	f one quadrant	1)	•	•		•		
Class II, Single Range, 7 500e / 6 000e	[g]	10.5	21	21	52.5	52.5	105	52.5	105
Class II, Single Range, 30 000e / 15 000e / 12 000e	[g]	7	14	14	35	35	70	35	70
Class III, Multi Interval, 3x10 000e	[g]	10.5	21	21	52.5	52.5	105	52.5	105
Minimum Weight typ.***	[g]	120	250	500	800	1000	2000	1000	2000

Readability in **bold** letters enable the use of an auxiliary indicating device to display d, where d = e/10

- * Requires installation by a METTLER TOLEDO Service Technician and appropriate environmental conditions
- ** at room temperature and stable environmental conditions without vibration and draft, with automated weight placement

Dimensional Drawings





	Models						
Dimensions [mm]	С	D	E	ES			
A	800	1000	1250	1500			
В	1000	1250	1500	1500			
С	625	890	1140	1390			
D	932	1110	1360	1360			
E	115-140	180-205	182-207	197-222			
_	40	60 v 60	60 v 60	60 × 60			

^{***} The minimum weight achievable depends on the settings of the weighing device, the tare vessel as well as the environment. The minimum weight of your device in situ can therefore be smaller or larger than the typical values published, for which METTLER TOLEDO takes no responsibility. The determination of the minimum weight on site is documented in GWP® Verification. The minimum weight is calculated at the minimum recommended readability and a process tolerance of 1%.

High Precision Floor Platforms General Specifications

Models			С	D	E	ES
Material						
	Stainless steel AISI304	Standard	•	•	•	•
Platform Material	Mild steel powder coated, blue	Standard • Standard • Standard				
	Mild steel galvanized	Standard		•	•	•
Platform Surface	Stainless Steel AlSl304, glas bead blasted Ra < 3 µm	Standard	•	•	•	•
	Stainless steel AlSI304	Standard	•	•	•	•
Load Plate Material	Mild steel galvanized	Option	•	•	•	•
	Stainless steel AlSI304, raisable	Option		•	•	•
	Stainless steel AlSi304, glas bead blasted, Ra < 3 µm	Standard	•	•	•	•
Load Plate Surface	Stainless steel brushed Ra < 0.8 µm	Option		•	•	•
Loud Fidio Garidoo	Stainless steel AlSI304 pattern	Option		•	•	•
	Desmopan (DP)	Standard	•		_	_
Foot	Stainless Steel AlSi304	Standard		•	•	•
Membrane	Silicone		•	•	•	•
		Standard	•			
Connecting Cable	Polyurethane (PU)	Standard	•	•	•	•
Connecting Cable Hazardous Area Category 3/Division 2 and Category 2/Division 1	Thermoplastic Polyether-Polyurethanytpe-U	Standard	•	•	•	•
Load Cell	Stainless Steel (AISI304), brushed, e-polished	Standard	•	•	•	•
Ingress Protection		'		·		
All PFK9 Weighing Platforms	IP66/68	Standard	•	•	•	•
Hazardous Area Approval*		'	·	'	'	
ATEX	Category 3GD	Option	•	•	•	•
	Category 2GD	Option	•	•	•	•
FM	Division 2	Option	•	•	•	•
	Division 1	Option	•	•	•	•
Resolution (The resolution is dependend on the	weighing platform model)					
Class III, Multi Interval, 3x10 000e Standard			•	•	•	•
Class II, Single Range, 1 x 6 000e / 1 x 7 500e			•	•	•	•
Class II, Single Range, 1 x 15 000e / 1 x 12 000e	9	Option	•	•	•	•
Class II, Single Range, 1 x 30 000e		Option	•**	•**	•**	•**
1 x 60 000d / 1 x 75 000d		Option	•	•	•	•
1 x 300 000d		Option	•	•	•	•
1 x 600 000d / 1 x 750 000d		Option	•	•	•	•
Temperature Range		- орнон				
Approved Application						
Accuracy Class II	0°C + 40°C					
Accuracy Class III	- 10°C + 40°C	1				
Non-Approved Application						
In Operation (Safe Area)	- 20°C + 60°C					
In Operation (Category 3/Division 2 and Category 2/Division 1)	ation (Category 3/Division 2 and					
For Storage	. ,					
or Storage - 20°C +70°C //orm up time (dependend on resolution)						
Typically 30 min						
Scale Interfaces						
SICSpro	MT - SICS command set, (Standard/Category3 /DIV2:	Standard				
	RS422, Category 2/DIV1: Ex-i CL)					
IDNet via ACC409xx adapter	SICSpro - IDNet signal convertor (cable)	Option Option				
Cable length Safe Area	0.5m, 2.5m, 5m, 10m, 20m					
Cable length Category 3 /Division 2 2.5m, 5m, 10m, 20m		Option				
Cable length Category 2 /DIV1 1.5m, 5m, 10m, 20m Option						

^{*} If intense electrostatic charging processes may be caused by applications or processes only use stainless steel platforms.

Model designation examples:

PFK989-C600 floor platform with frame in stainless steel, C-Size (800 mm x 1000 mm), capacity 600kg PFK988-E3000 floor platform with frame in mild steel galvanized, E-Size (1250 mm x 1500 mm), capacity 3000kg

Connection to Terminals



Terminals with SICSpro interface that directly connect to PFK9: IND890, IND570, IND690 (xx), ICS4_5; ICS685; ICS4_9, ICS689



Terminals with IDNet interface that require ACC409xx adapter: IND4_9(xx); IND560(xx); IND690 (xx); IND780(xx); ID5; ID7; ID30 (ID5, ID7 and ID30 for non-approved applications only)

^{**} Requires installation by a METTLER TOLEDO Service Technician and appropriate environmental conditions and appropriate weights.

Accessories

Article Number	Designation	Description	Picture			
30242214	Quick Pit C Model galvanized	930 x 1210 mm				
30242215	Quik Plt C Model stainless steel	930 x 1210 mm				
30242216	Quick Pit D Model galvanized	1130 x 1380 mm	and the second			
30242217	Quick Pit D Model stainless steel	1130 x 1380 mm				
30242218	Quick Pit E Model galvanized	1390 x 1640 mm				
30242219	Quick Pit E Model stainless steel	1390 x 1640 mm				
30242220	Quick Pit ES Model galvanized	1640 x 1640 mm				
30242221	Quick Pit ES Model stainless steel	1640 x 1640 mm				
503638	Ramp C Model galvanized pattern					
599204	Ramp C Model stainless steel pattern	For C Model only				
599198	Ramp C Model stainless steel smooth					
30242223	Cable M12 RS422 SICSpro 12P/6P 2,5m					
30242224	Cable M12 RS422 SICSpro 12P/6P 5m					
30242226	Cable M12 RS422 SICSpro 12P/6P 10m	Cables for safe area				
30242225	Cable M12 RS422 SICSpro 12P/6P 20m					
30242227	Cable M12 RS422 SICSpro 12P/6P 100m					
30242229	Cable M12 RS422 SICSpro 2,5m Ex2					
30242230	Cable M12 RS422 SICSpro 5m Ex2	Cables for hazardous area (Cat 3, DIV 2)				
30242231	Cable M12 RS422 SICSpro 10m Ex2	Cubies for fluzurdous died (Cdi 3, Div 2)				
30242232	Cable M12 RS422 SICSpro 20m Ex2					
30267158	Cable M12 6p 1,5m Ex1					
30267159	Cable M12 6p 5m Ex1	Cables for hazardous area (Cat 2, DIV1)	MIE TO THE TOTAL THE TOTAL TO T			
30267190	Cable M12 6p 10m Ex1	Cubies for fluzurdous died (Cdi 2, Div1)				
30337109	Cable M12 6p 20m Ex1					
00503617	Load plate, D-size, mild steel powder coated					
00503618	Load plate, D-size, mild steel galvanized					
00503619	Load plate, D-size, stainless steel					
00503620	Load plate, E-size, mild steel powder coated					
00503621	Load plate, E-size, mild steel galvanized					
00503622	Load plate, E-size, stainless steel					
00504504	Load plate, ES-size, mild steel powder coated		2			
00504505	Load plate, ES-size, mild steel galvanized					
00504506	Load plate, ES-size, mild steel galvanized					
22026963	ACC409xx	Adapter to convert SICSPro signal into IDNet for use in safe area and Category 3				

METTLER TOLEDO Service

Our extensive service network is among the best in the world and ensures maximum availability and service life of your product.



Quality certificate ISO 9001 Environment certificate ISO 14001

www.mt.com.