CERTIFICATE OF CONFORMITY



1. HAZARDOUS LOCATION ELECTRICAL EQUIPMENT PER CANADIAN REQUIREMENTS

Certificate No: 2.

FM16CA0119X

3. **Equipment:** (Type Reference and Name) M400 Series, Multi-parameter Transmitter

Name of Listing Company: 4.

Mettler-Toledo GmbH

5. Address of Listing Company:

Im Hackacker 15 (Industrie Nord) CH-8902 Urdorf, Canton of Zurich

Switzerland

The examination and test results are recorded in confidential report number: 6.

3046275 dated 30th October 2015

7. FM Approvals LLC, certifies that the equipment described has been found to comply with the following Approval standards and other documents:

> CSA-C22.2 No. 94:1976, CSA-C22.2 No. 213-M1987:2013, CSA-C22.2 No. 60079-0:2015, CSA-C22.2 No. 60079-11:2014, CSA-C22.2 No. 60529-05:2010, CSA-C22.2 No. 61010-1:2004

- 8. If the sign 'X' is placed after the certificate number, it indicates that the equipment is subject to specific conditions of use specified in the schedule to this certificate.
- This certificate relates to the design, examination and testing of the products specified herein. The FM Approvals surveillance audit program has further determined that the manufacturing processes and quality control procedures in place are satisfactory to manufacture the product as examined, tested and Approved.

Certificate issued by:

J./E. Marquedant

VP, Manager - Electrical Systems

9 January 2020

To verify the availability of the Approved product, please refer to www.approvalguide.com

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Mar 16) Page 1 of 8



Member of the FM Global Group

to Canadian Certificate Of Conformity No: FM16CA0119X

10. Equipment Ratings:

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire HART electronics) equipment is certified to the following classification(s).

Intrinsically safe apparatus for use in Class I, Division 1, Groups A, B, C and D, Class II, Division 1, Group E, F and G, Class III, Division 1, in accordance with manufacturer's Control Drawing; equipment protection by intrinsic safety Ex ia for use in Class I, Zone 0, Group IIC, in accordance with manufacturer's Control Drawing, hazardous locations; and ordinary locations with an ambient temperature rating of -20 °C to +60 °C, indoor and outdoor (Type 4X; IP66) environments.

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire FF/PA and FISCO FF/PA electronics) equipment is certified to the following classification(s).

Intrinsically safe apparatus for use in Class I, Division 1, Groups A, B, C and D, Class II, Division 1, Group E, F and G, Class III, Division 1, in accordance with manufacturer's Control Drawing; intrinsically safe apparatus with fieldbus intrinsically safe concept wiring for use in Class I, Division 1, Groups A, B, C and D, Class II, Division 1, Groups E, F and G, Class III, Division 1, in accordance with manufacturer's Control Drawing; equipment protection by intrinsic safety Ex ia for use in Class I, Zone 0, Group IIC, in accordance with manufacturer's Control Drawing; equipment protection by intrinsic safety Ex ia with fieldbus intrinsically safe concept wiring for use in Class I, Zone 0, Group IIC, in accordance with manufacturer's Control Drawing, hazardous locations; and ordinary locations with an ambient temperature rating of -20 °C to +60 °C, indoor and outdoor (Type 4X; IP66) environments.

In type of protection suitable equipment, the multi-parameter transmitter (M400 Series, 2-Wire electronics) equipment is certified to the following classification(s).

Suitable equipment for use in Class I, Division 2, Groups A, B, C and D, hazardous locations; and ordinary locations with an ambient temperature rating of -20 °C to +60 °C, indoor and outdoor (Type 4X; IP66) environments.

11. The marking of the equipment shall include:

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire HART electronics) equipment is labelled with the following marking(s).

Exia, SÉCURITÉ INTRINSÈQUE

Class I, II, III, Division 1, Groups A, B, C, D, E, F, G T4

Class I, Zone 0, Ex ia IIC T4 Ga

Ta = -20 °C to +60 °C

Control Drawing No. 12112601/12112602/12112604; Entity; Type 4X; IP66

WARNING - POTENTIAL ELECTROSTATIC CHARGING HAZARD - SEE INSTRUCTIONS

AVERTISSEMENT - DANGER POTENTIEL DE CHARGES ÉLECTROSTATIQUES - VOIR INSTRUCTIONS

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Mar 16) Page 2 of 8



Member of the FM Global Group

to Canadian Certificate Of Conformity No: FM16CA0119X

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire FF/PA and FISCO FF/PA electronics) equipment is labelled with the following marking(s).

Exia, SÉCURITÉ INTRINSÈQUE

Class I, II, III, Division 1, Groups A, B, C, D, E, F, G T4

Class I, Zone 0, Ex ia IIC T4 Ga

Ta = -20 °C to +60 °C

Control Drawing No. 12112602/12112603/12112604; Entity; FISCO Field Device; Type 4X; IP66
WARNING – POTENTIAL ELECTROSTATIC CHARGING HAZARD – SEE INSTRUCTIONS
AVERTISSEMENT – DANGER POTENTIEL DE CHARGES ÉLECTROSTATIQUES – VOIR INSTRUCTIONS

In type of protection suitable equipment, the multi-parameter transmitter (M400 Series, 2-Wire electronics) equipment is labelled with the following marking(s).

Class I, Division 2, Groups A, B, C, D T4A

Ta = -20 °C to +60 °C

Type 4X; IP66

WARNING – POTENTIAL ELECTROSTATIC CHARGING HAZARD – SEE INSTRUCTIONS AVERTISSEMENT – DANGER POTENTIEL DE CHARGES ÉLECTROSTATIQUES – VOIR INSTRUCTIONS WARNING – SUBSTITUTION OF COMPONENTS MAY IMPAIR SUITABILITY FOR DIVISION 2 AVERTISSEMENT – RISQUE D'EXPLOSION. LE REMPLACEMENT DE COMPOSANTS PEUT NUIRE À LA CONFORMITÉ DE DIVISION 2.

WARNING – EXPLOSION HAZARD – DO NOT DISCONNECT EQUIPMENT WHEN A FLAMMABLE OR COMBUSTIBLE ATMOSPHERE IS PRESENT

AVERTISSEMENT – RISQUE D'EXPLOSION – NE PAS DÉBRANCHER L'ÉQUIPEMENT QUAND UNE ATMOSPHÈRE INFLAMMABLE OU COMBUSTIBLE EST PRÉSENT

12. Description of Equipment:

General – The M400 Series Multi-parameter Transmitter is designed for industrial and hazardous (classified) location applications. Collecting physical signals such as pH, dissolved oxygen, electrical conductivity (resistivity), process temperature, and process voltage, etc., it converts those signals into a standard 4-20 mA HART electrical signal, or Foundation FieldbusTM/Profibus (FF/PA) communication signal. It is powered by 2-wire and can be connected to analog sensor or digital sensor to delivers 4-20 mA HART output signal or FF/PA BUS communication signal, representing pH, dissolved oxygen, electrical conductivity (resistivity), process temperature, and process voltage, etc. The consuming current running on the extent permitted does not depend on supply voltage, but depends on the measured value.

Depending on the model, the transmitter can be configured with the software or keys, for different parameter measurement or several separate measurements combined together.

The M400 2-Wire Multi-parameter Transmitter exists in three versions, but has identical hardware. They are all 2-wire 4-20 mA loop powered transmitters with a second (passive) current output, analog and ISM (digital) sensor input, analog 4-20 mA current input for pressure compensation of oxygen measurement, two digital inputs for e.g. HOLD, two open collector outputs for alarm, set points, etc.

The M400 FF/PA Multi-parameter Transmitter exists in two versions, but has identical hardware. They are all 2-wire FF or PA BUS loop powered transmitters with analog and ISM (digital) sensor input, analog 4-20 mA current input for pressure compensation of oxygen measurement.

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Mar 16) Page 3 of 8



Member of the FM Global Group

to Canadian Certificate Of Conformity No: FM16CA0119X

The transmitter is powered by 2-wire and can be connected to analog sensor or digital sensor to deliver 4-20 mA HART or Foundation FieldbusTM/Profibus (FF/PA) output signal, representing electrical conductivity (resistivity), pH, dissolved oxygen, process temperature, and process voltage, etc.

Construction – The multi-parameter transmitter enclosure is constructed of an aluminum alloy, ADC12, housing (front cover and base) with an additional internal plastic housing incorporating the electronics subassembly attached to the rear/inside of the enclosure front cover.

On the outside/external front cover, there is one LCD video graphics array color touch screen display and five membrane buttons which conveys measuring data and setup information.

The enclosure base is equipped with five 0.75 in. diameter smoothly well-rounded openings for field wiring (M20 x 1.5 and NPT cable glands, hazardous (classified) location certified plugs, and 1/2 in. NPT conduit connections), provided for external field wiring connections. The enclosure front cover and base are internally bonded together. The enclosure base is equipped with an internal and external threaded ground terminal for installation practices.

The internal threaded ground terminal is equipped with a factory-installed fixed 6 in. flying leadwire for installation practices when using metallic raceways, metallic cable glands or metallic rigid conduit.

The electronics assembly of the vibration level switch is constructed from one of two designs. The C300KK-HART indicates the electronics version for the 2-Wire 4-20 mA HART electrical signal design. The C300KK-FF/PA indicates the electronics version for the 2-Wire Foundation FieldbusTM/Profibus (FF/PA) communication signal design.

For more specifics concerning construction and description details of the multi-parameter transmitter, reference the manufacturer's sales literature and specification sheets.

Ratings – The equipment is certified to the following ratings.

The ambient operating temperature range is -20 °C to +60 °C in types of protection intrinsically safe apparatus and suitable equipment; each when properly mounted and installed.

The equipment is marked for appliance protection class I, designated for installation transient overvoltages up to levels of overvoltage category I, and environmentally classified as pollution degree 3.

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire HART electronics) equipment is connected to a certified intrinsically safe linear circuit with the following maximum entity parameter values.

Digital-In1 Terminals (1, 2) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci \approx 0, Li \approx 0, Pi = 0.8 W

Digital-In1 Terminals (3, 4) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci \approx 0, Li \approx 0, Pi = 0.8 W

Analog-Out1 Terminals (10, 11) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci \approx 0, Li \approx 0, Pi = 0.8 W

Analog-Out2 Terminals (12, 13) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci \approx 0, Li \approx 0, Pi = 0.8 W

OC-Out1 Terminals (6, 7) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci = 15 nF, Li ≈ 0 , Pi = 0.8 W

OC-Out2 Terminals (8, 9) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci = 15 nF, Li \approx 0, Pi = 0.8 W

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Mar 16) Page 4 of 8



Member of the FM Global Group

to Canadian Certificate Of Conformity No: FM16CA0119X

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire FF/PA electronics) equipment is connected to a certified intrinsically safe linear circuit with the following maximum entity parameter values.

Barrier Terminals (10, 11) are:

Vmax (Ui) = 24 VDC, Imax (Ii) = 200 mA, Ci = 3 nF, Li \approx 0, Pi = 1.2 W

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire FISCO FF/PA electronics) equipment is connected to a certified intrinsically safe linear circuit with the following maximum fieldbus intrinsically safe concept parameter values.

Field Device Terminals (10, 11) are:

Vmax (Ui) = 17.5 VDC, Imax (Ii) = 380 mA, Ci = 3 nF, Li \approx 0, Pi = 5.32 W

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire HART, FF/PA and FISCO FF/PA electronics) equipment is connected to a certified intrinsically safe linear circuit with the following maximum entity parameter values.

Conductivity Sensor Terminals (A, B, E, G) are:

Voc (Uo) = 5.88 VDC, Isc (Io) = 29 mA, ICa (ICo) = 2.5 IF, ILa (ILo) = 1 mH, IPo = 43 mW

Inductive Conductivity Sensor Terminals (D. E. F. G. H) are:

Voc(Uo) = 5.36 VDC, Isc(Io) = 17.2 mA, $Ca(Co) = 3.2 \mu\text{F}$, La(Lo) = 1 mH, Po = 23 mW

pH Sensor Terminals (A, E, G) are:

Voc $(U_0) = 5.88 \text{ VDC}$, $I_{SC}(I_0) = 1.3 \text{ mA}$, $I_{Ca}(C_0) = 2.1 \mu\text{F}$, $I_{Ca}(L_0) = 5 \text{ mH}$

Dissolved Oxygen Sensor Terminals (B, D, H) are:

Voc (Uo) = 5.88 VDC, Isc (Io) = 29 mA, Ica (Ico) = 2.5 ImF, Ica (Ico) = 1 mH, Ico = 43 mW

Temperature Sensor Terminals (I, J, K) are:

Voc (Uo) = 5.88 VDC, Isc (Io) = 5.4 mA, Ca (Co) = 2 μ F, La (Lo) = 5 mH, Po = 8 mW

Temperature Sensor Terminals with Inductive Conductivity (I, J, K) are:

Voc (U0) = 5.88 VDC, Isc (I0) = 4.9 mA, ICa (I0) = 2 IF, ILa (I0) = 5 mH, IPo = 6.6 mW

One-Wire Sensor Terminal (L) are:

Voc(Uo) = 5.88 VDC, Isc(Io) = 22 mA, $Ca(Co) = 2.8 \mu F$, La(Lo) = 1 mH, Po = 32 mW

RS485 Sensor Terminals (N, O) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci = 0.7 μ F, Li \approx 0, Pi = 0.8 W

Voc(Uo) = 5.88 VDC, Isc(Io) = 54 mA, $Isc(Co) = 1.9 \mu F$, Isc(Lo) = 1 mH, Isc(Po) = 80 mW

Analog-In Terminals (P, Q) are:

Vmax (Ui) = 30 VDC, Imax (Ii) = 100 mA, Ci = 15 nF, Li \approx 0, Pi = 0.8 W

In type of protection suitable equipment, the multi-parameter transmitter (M400 Series, 2-Wire electronics) equipment is connected to limited output Class 2 circuits and power source with the following nominal external supply values.

Power Supply and Signal Circuit Terminals (1, 2) are:

Vmax (Ui) = 14-30 VDC, Imax (Ii) = 100 mA, Pi = 0.8 W

Um = 250 V maximum

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Mar 16) Page 5 of 8



Member of the FM Global Group

to Canadian Certificate Of Conformity No: FM16CA0119X

Model Codes – The equipment is identified with the following model code structure.

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire HART electronics) equipment is designated with the following model code(s).

M400, 2-Wire HART Transmitter

Reference Control Drawing No. 12112601/12112602/12112604 for Entity Parameter values

| Part Number | Type |
|-------------|---|
| 30 025 515 | M400/2XH Multi-parameter (pH, O2, conductivity) 1-Channel ISM & Analog Transmitter for |
| | Dissolved Measurement |
| 30 025 516 | M400G/2XH Multi-parameter (pH, O2, conductivity) 1-Channel ISM & Analog Transmitter for |
| | Dissolved and Gas Measurement |
| 30 256 307 | M400/2XH Multi-parameter (Conductivity Ind) 1-Channel Analog Transmitter for Conductivity |
| | Measurement |
| 30 256 317 | M400/2XH Type 1 Multi-parameter (pH, Conductivity) 1-Channel ISM & Analog Transmitter |
| | with Limited Functionality |
| 30 568 985 | M400/2XH Type 2 Multi-parameter (pH, O2, Conductivity) 1-Channel ISM & Analog |
| | Transmitter with Limited Functionality |
| 30 568 986 | M400/2XH Type 3 Multi-parameter (pH, O2, Conductivity) 1-Channel ISM & Analog |
| | Transmitter with Limited Functionality |

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire FF/PA and FISCO FF/PA electronics) equipment is designated with the following model code(s).

M400, 2-Wire FF/PA Transmitter

Reference Control Drawing No. 12112602/12112603/12112604 for Entity Parameter values Reference Control Drawing No. 12112602/12112603/12112604 for FISCO Parameter values

| Part Number | Туре |
|-------------|--|
| 30 026 616 | M400 FF Multi-parameter (pH, O2, conductivity) 1-Channel ISM & Analog Transmitter for |
| | Dissolved Measurement |
| 30 026 617 | M400 PA Multi-parameter (pH, O2, conductivity) 1-Channel ISM & Analog Transmitter for |
| | Dissolved and Gas Measurement |
| 30 256 309 | M400 FF Multi-parameter (Conductivity Ind) 1-Channel Analog Transmitter for Conductivity |
| | Measurement |
| 30 256 310 | M400 PA Multi-parameter (Conductivity Ind) 1-Channel Analog Transmitter for Conductivity |
| | Measurement |

In type of protection suitable equipment, the multi-parameter transmitter (M400 Series, 2-Wire electronics) equipment is designated with the following model code(s).

M400, 2-Wire Transmitter

| Part Number | Type |
|-------------|--|
| 30 025 514 | M400/2H Multi-parameter (pH, O2, conductivity) 1-Channel ISM & Analog Transmitter for |
| | Dissolved Measurement |
| 30 256 312 | M400/2H Multi-parameter (Conductivity Ind) 1-Channel Analog Transmitter for Conductivity |
| | Measurement |

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com

F 348 (Mar 16) Page 6 of 8



Member of the FM Global Group

to Canadian Certificate Of Conformity No: FM16CA0119X

13. Specific Conditions of Use:

In type of protection intrinsically safe apparatus, the multi-parameter transmitter (M400 Series, 2-Wire HART, FF/PA and FISCO FF/PA electronics) equipment is designated with the following specific conditions of use.

- 1. Potential Electrostatic Charging Hazard To prevent the risk of electrostatic sparking, the non-metallic surface should only be cleaned with a damp cloth.
- 2. The overlay switch of the multi-parameter transmitter shall be protected from high risk of mechanical danger and ultraviolet light.
- 3. The panel mount gasket has not been tested for type of protection Type 4X, IP66 or Class II and III. Type of protection Type 4X, IP66 and Class II and III refers to the transmitter enclosure only.
- 4. Enclosures containing aluminum constitute a potential risk of ignition by impact or friction. Care must be taken into account during installation and use to prevent impact or friction.

In type of protection suitable equipment, the multi-parameter transmitter (M400 Series, 2-Wire electronics) equipment is designated with the following specific conditions of use.

- 1. Potential Electrostatic Charging Hazard To prevent the risk of electrostatic sparking, the non-metallic surface should only be cleaned with a damp cloth.
- 2. The overlay switch of the multi-parameter transmitter shall be protected from high risk of mechanical danger and ultraviolet light.
- 3. The panel mount gasket has not been tested for type of protection Type 4X, IP66 or Class II and III. Type of protection Type 4X, IP66 and Class II and III refers to the transmitter enclosure only.
- 4. Enclosures containing aluminum constitute a potential risk of ignition by impact or friction. Care must be taken into account during installation and use to prevent impact or friction.

14. Test and Assessment Procedure and Conditions:

This Certificate has been issued in accordance with FM Approvals Canadian Certification Scheme.

15. Schedule Drawings:

A copy of the technical documentation has been kept by FM Approvals.

16. **Certificate History:**

Details of the supplements to this certificate are described below:

| Date | Description |
|----------------------------|---|
| 30th October 2015 | Original Issue. |
| 15 th July 2016 | Supplement 2: Report Reference: RR205767, dated 15 th July 2016. Description of the Change: Addition of the new sensor printed circuit board for adaption to the existing communication printed circuit boards (HART, FF/PA); the new sensor printed circuit board has larger copper field and does not introduce any new component package. Assembly document and model code updates – the actual change is made to the entire certificate and the full document is issued to the holder. |

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com <a href="mai

F 348 (Mar 16) Page 7 of 8



Member of the FM Global Group

to Canadian Certificate Of Conformity No: FM16CA0119X

| Date | Description | |
|------------------------------|--|--|
| 9 th January 2020 | Supplement 3: Report Reference: RR221779, dated 9 th January 2020. Description of the Change: Addition of the new M400/2XH 2-wire transmitter, firmw variant of existing part number 30025515, with restrictions in sensor types. Namep document and model code update. | |
| | LIM Whin Appling | |

FM Approvals

FM Approvals

THIS CERTIFICATE MAY ONLY BE REPRODUCED IN ITS ENTIRETY AND WITHOUT CHANGE

FM Approvals LLC. 1151 Boston-Providence Turnpike, Norwood, MA 02062 USA
T: +1 (1) 781 762 4300 F: +1 (1) 781 762 9375 E-mail: information@fmapprovals.com www.fmapprovals.com