

### Industrial Compact Systems The ICS4 and ICS6 Family

Modular and Versatile Fast and Precise Robust and Reliable For Dry and Wet Environments



# **Tailored Solutions**

for Your Industrial Applications



# **One Family** Versatile Use

The ICS product family is a highly modular product range consisting of a large

#### Maximum Versatility

The ICS6 Excellence level indicators enable you to manage complex systems with a high degree of flexibility and easy setup. With the ability to control up to four platforms and a wide range of interface options, your investment will help maximize profits while providing long-life, high uptime quality weighing equipment.

### | Highest Throughput variety of indicators and platforms to best fulfill your specific requirements. From The ICS4 Standard level scales are simple weighing to integrated solutions with multiple components including third available with a variety of keypad party devices – a wide range of configurations are possible. 0000 and housing options to allow a customized solution perfectly tailored to your specific weighing tasks. The software supports a range of applications including counting, over/ under checkweighing, dynamic weighing, and portioning. The graphic display with colorWeight® The right solution tailored to the specific feature ensures high throughput with needs of your application in any industrial easy-to-read error free results. environment. ICS689 ICS685 ICS469 ICS465 ICS425 **METTLER TOLEDO** Filling, Classifying, Data/User Management Counting, Over/Under-Checkweighing, Portioning **Basic Weighing** Wet, Harsh, Hygienic Dry, Dusty Manufacturina Food, Chemical, Pharmaceutical

### **Reliable Weighing**

Numerous workplaces in different industrial market segments require only basic weighing solutions. Choose the easy-to-use basic models of the ICS family which provide all the necessary functions, proven industrial quality and reliable weighing results day in and day out.



Application Environment Industry

# **Optimize Your Processes** Meet Your Toughest Requirements

The ICS scale family is designed to integrate easily into your weighing process. It offers a broad range of solutions for your checkweighing, counting or quality assurance applications. Make your choice, select your optimal combination and raise your throughput, increase process security and improve your product and delivered quality.

### Reliable Counting

When verifying inventory, packaging or confirming production quantities, every part is important. METTLER TOLEDO counting solutions ensure that only the right number of parts are delivered to the customer. The ICS scale family provides solutions to make parts-counting applications fast, accurate and cost effective.



Portioning and

Classifying

The ICS product family supports fast and efficient portioning or classifying processes. Depending on the preferred working procedure the operator can choose between different modes. Whether filling small containers placed on the platform, or using the powerful take away mode feature for filling without a keystroke, the ICS scales help to speed up productivity up to 20%.





When product integrity matters, check-weighing is a fast and cost-effective quality assurance method. Whether you need to detect missing components of assemblies or whole shipments, control the completeness of castings or verify the amount of lubricants applied, the ICS scales provide clear information as to whether the quality specifications are met and the shipment is complete.



## **Flexible and Mobile**

All ICS4 and ICS6 models can be equipped an optional built-in rechargeable battery, the scales can easily be moved and placed where they best fit into the process. The state of the art Lithium-Ion battery technology ensures many hours of continuous operation.




# High Throughput and Reliable Processes

Speed counts in today's competitive environment. Manufacturers need not only to deliver error free, high-quality products, but to produce with high throughput. With the ICS4 and ICS6 Industrial Compact Scales you can achieve both. Benefit from an intuitive user menu with easy-to-use weighing and counting applications and superior weighing performance for fast and accurate results.



Avoid Errors

**Ensure Accuracy** 



While counting pieces or checking completeness using a weighing system, operators typically have to concentrate intensely on the indicator display which slows down their process. The colorWeight<sup>®</sup> function clearly indicates, using different colors, when the target is reached. This eases the operator's concentration, speeds up the task and saves time and money.



Intuitive user menus and efficient user prompting prevent operator errors and fatigue during repetitive tasks. Configurable softkeys allow fast access to frequently used functions. Users are guided through the weighing and counting tasks in different languages. Set user profiles and deactivate unused hardkeys to make operation traceable, secure and error free.



ICS compact scales feature highperformance weighing technology. This includes MonoBloc<sup>®</sup> electromagnetic force-compensation load cells, built for long service life, extreme ruggedness and outstanding accuracy. These high-precision load cells deliver accurate results fast and reliable measurements day in and day out for increased productivity and minimum downtime.



# colorWeight<sup>®</sup> Speeds up production

Save time and money with the smart colored display making weighing applications such as completeness checks, portioning, classifying and counting simple, fast and less error prone. The colorWeight<sup>®</sup> display indicates at a glance if weight or count is below, within or above target.

# colorWeight® 101 rs above target



# **Resist Wet and Harsh 24/7** for Fast and Complete Washdown

From light wet to harsh washdown conditions - it doesn't matter. The stainless steel platforms and indicators of the ICS4 and ICS6 series provide a flexible and rugged solution for a wide range of weighing tasks. All parts have been engineered and manufactured according to the latest hygienic design guidelines resulting in a construction without closed cavities or sharp edges and with minimum horizontal surfaces. This allows easy, fast and efficient cleaning.

## Designed for Harsh Conditions



Equipment used in hygienic sensitive areas such as food production must be designed and installed according to sound sanitary principles. The ICS689 product line is designed using the latest hygienic design guidelines including EHEDG or NSF. This includes a double sealed, IP69k protected indicator.

EHEDG: European Hygienic Engineering & Design Group NSF: National Sanitation Foundation

## Configurable to your Environment

Whether your processes require only wet wiping or heavy washdown procedures, the appropriate load cell according to your cleaning requirements can be chosen. Selections include an aluminum potted load cell with IP65 protection up to a hermetically sealed stainless steel load cell (IP68/IP69k) for permanently wet environments.



Open and

The stainless steel construction is built to withstand wet and harsh environments. Designs feature open construction. Optimally placed and independently adjusted overload stops and additional side impact protection maintain your load cell's accuracy and the efficiency of your processes in rough industrial environments.



## **Built for Efficient Cleaning**

IP69K protected indicators and hermetic sealed loadcells engineered in conjunction with platform designs conforming to the latest hygienic guidelines, enable efficient and easy cleaning access to all areas.

- Open platter construction
- Full stainless steel
- Reduced flat surfaces
- Die-casting load cell mounting plate
- Reduced cavities
- No exposed threads



**ÍP68** 





# **Integrated Data Handling** Fast, Reliable and Traceable

Accurate weighing is important, but so is weighing data integration. Easily manage articles, materials and related parameters on the scale or a connected computer. Capture weighing results and other relevant data on the scale, print them on customizable labels or securely transfer them to your data management system to document and monitor your process.

#### **Proven Traceability**

Whether legally required or specified by customers, today traceable processes are standard. Ensure full traceability of your weighing process with a comprehensive set of features such as

- Identification of arti cles and materials via barcode reader
- Definition of tolerances and tare values in an article database
- Secure storage of weighing data and related parameters
- Accurate batch identification with customizable label printing



#### Easy Connectivity

Connect your scale via Ethernet or USB for easy data transfer and connect a barcode reader (via RS232 or USB) for secure material identification.







#### Powerful Database

Article

Screw 1

Store your articles and materials in the scale-embedded database together with relevant parameters such as target weight or count, tolerances, tare values or average piece weights.

## Secure Data Handling Weighing data including article ID or operator ID, stored in a protected me

Weighing data including date/time, article ID or operator ID, is securely stored in a protected memory. Manage access to the scale and weighing data with multi-level user access rights.

#### **Customizable Label Printing**


Customize printing labels to meet customer and industry requirements. Ensure traceable printing of weighing or counting results and process identification.

#### **Real-time Monitoring**

Visualize your weighing results from anywhere in real-time with the software Collect<sup>+</sup>. Capture statistical quality control data with FreeWeigh. Net PC software.







#### Efficient Data Management

Manage articles and related data directly on the scale or use the PC software DatablCS to easily set-up and manage your article database centrally for multiple scales.

# Safe and Accurate Weighing In Hazardous Areas

Three considerations are important in potentially explosive environments: Is the weighing process safe and compliant? Does it deliver accurate results? And can it be handled efficiently? The intrinsically safe ICS4\_6x-Series combi bench scales deliver all three aspects and ensure safe, accurate and efficient weighing in hazardous areas.

### Full Protection

**Highest Accuracy** 

Best Usability



The ICS4\_6x-Series combi bench scales enable safe and efficient operations in hazardous areas classified as Zone 1/21 and Division 1. The intrinsically safe product design ensures the highest level of safety and compliance with the latest hazardous area requirements. In addition, the scales feature a compact design and can be easily maintained.



High-precision weighing in a hazardous area is a challenge. The ICS4\_6x-Series enable industry leading accuracy of up to 750.000d in Zone 1/21, Division 1. When tolerances are tight, these scales deliver the precision to ensure consistently accurate results without compromising safety.



The scales can be flexibly configured to ensure ergonomic and efficient operation. An intuitive operating philosophy provides easy and secure handling of even complex weighing applications in the hazardous area. The colorWeight® functionality of the ICS466x improves speed and control of weighing tasks by immediately indicating if a result is within tolerance.



## **Proven Compliance**

The ICS4\_6x-Series are approved according global and local standards. IECEx, ATEX and FMC+US are approvals for use in hazardous areas classified as Zone 1/21 and Division 1. Regular audits of the METTLER TOLEDO production facilities by the certification bodies verify that standards are applied and safety is ensured.





# **2** Interface Options / Accessories

Optional Data Interfaces	RS232, RS422/485,
Optional Scale Interfaces	digital SICSpro, digita
Accessories	Choose from various
	packs, relays for diai

# **3** Combine with the best fit platform for dry environment

#### Standard Resolution, ICS4\_5/685 Compact Scales PBD555

	1										
Platform Size (Loadplate size)	0.6 kg	3 kg	6 kg	12 kg	15 kg	30 kg	35 kg	60 kg	120 kg	300 kg	600 kg
SM 206x247 (200x240 mm)		•	•								
LA 247x357 (240x350 mm)					•		•				
Approved readability (up to 7,500e)		0.5 g	1 g		2 g		5 g				
Recommended readability at max. resolution (up to 75,000d)		0.05 g	0.1 g		0.2 g		0.5 g				
Ingress Protection	IP65 (o)	ptional)									

### High Precision, ICS4\_5/685 Compact Scales



PBK785												
Platform Size (Loadplate size)	0.6 kg	3 kg	6	kg	12 kg	15 kg	30 kg	35 kg	60 kg	120 kg	300 kg	600 kg
XS 206x247 (130x160 mm)	•	•	•									
SM 206x247 (200x240mm)				•								
LA 247x357 (240x350 mm)						•		•				
Approved readability (up to 60,000e)	0.1 g	0.1 g	0.1 g	1 g		1 g		1 g				
Recommended readability at max. resolution (up to 610,000d)	0.01 g	0.01 g	0.01 g	0.1 g		0.1 g		0.1 g				
Ingress Protection	IP65 (o	ptional)										

## High Capacity, ICS4\_5/685 Compact Scales

PBD	655											
Plat	form Size	0.6 kg	3 kg	6 kg	12 kg	15 kg	30 kg	35 kg	60 kg	120 kg	300 kg	600 kg
A	240x300 mm			•	•							
BB	300x400 mm						•		•			
В	400x500 mm								•	•		
BC	500x650 mm								•	•	•	
CC	600x800 mm								•	•	•	•
•••	roved readability 00e)			1 g	2 g		5 g		10 g	20 g	50 g	100 g/ 200 g <sup>1)</sup>
	ommended readability at resolution (60,000d)			0.1 g	0.2 g		0.5 g		1 g	2 g	5 g	10 g
Ingre	ess Protection	IP65								-		

\* For counting applications; process tolerance 1%; probability 95.4%

# **Compact Weighing Systems** For Dry and Dusty Environments

The ICS4\_5 and ICS685 compact scales are the perfect fit for your applications in dry or dusty environment. Whether you look for a scale for simple weighing, advanced counting or quality control applications you will find the perfect solution for your specific needs.

# Choose an Application / Indicator

				2000-0	
Model	ICS425	ICS435	ICS445	ICS465	ICS685
Applications	Basic Weighing	Basic Weighing	Basic Weighing Counting	Basic Weighing Counting Over/Under Checkweighing	Basic Weighing Counting Over/Under Check- weighing Filling/Dosing Classifying Formulation SpeedWeigh Pick&Pack
Color TFT display					•
colorWeight <sup>®</sup>				•	•
Configurable soft keys			•	•	•
Numeric (n)/alphanumeric (a) keypad		n		n	a
Additional interface options	1	1	1	1	3
Attachable platforms	1	1	2	2	4*

\* Maximum 2 analog, or 2 IDNet platforms respectively 1 analog plus 1 IDNet

#### **General Specifications**

300,000d; 7,500e, OIML/10,000d, NTEP						
ICS4_5: LCD liquid crystal graphical display with backlighting ICS685: Color TFT display 320 x 240 pixels						
Tactile-touch membrane keypad (PET), scratch-resistant material						
Die-cast aluminium						
IP65						
100–240 VAC; optional battery 12 V/2.5 A						
1 RS232						

\*\* for digital platforms, the resolution is defined by the respective platform



, USB device/host, Ethernet, Digital I/O (4 Inputs + 4 Outputs)

tal IDNet, analog (max. 2 analog, or 2 IDNet resp. 1 analog + 1 IDNet) accessories such as wall bracket, columns/stands, roller tops, printers, battery ital I/O, barcode scanners and much more

# **Z** Interface Options / Accessories

<b>Optional Data Interfaces</b>	RS232, RS422/485,
<b>Optional Scale Interfaces</b>	digital SICSpro, digita
Accessories	Choose from various tery packs, relays for

3 kg

٠

•

6 kg

٠

٠

6 kg

1 g

0.1 g

# **Your Customized Solution** Wet and Harsh Environments

The ICS4\_9 and ICS689 compact systems are the perfect solution for any application in wet and harsh environment. The rugged stainless steel design of all indicators and platforms with high ingress protection guarantees long lifetime and allows frequent and intensive cleaning.

## Choose an Application / Indicator

	2845		2825	28255	
Model	ICS429	ICS439	ICS449	ICS469	ICS689
Applications	Basic Weighing	Basic Weighing	Basic Weighing Counting Over/Under Checkweighing	Basic Weighing Counting Over/Under Checkweighing	Basic Weighing Counting Over/Under Check- weighing Filling/Dosing Classifying Formulation SpeedWeigh Pick&Pack
Color TFT display					•
colorWeight®			•	•	•
Five configurable soft keys			•	•	•
Numeric (n)/alphanumeric (a) keypad		n		n	a
Additional interface options	1	1	1	1	3
Attachable platforms	1	1	2*	2*	4**

\* Connection of a second scale to ICS449 and ICS469 is limited to SICSpro- or SICS-interface

\*\* Maximum 2 analog, or 2 IDNet platforms respectively 1 analog plus 1 IDNet

#### **General Specifications**

Resolution for analog platforms***	Up to OIML 2x3,000e/ NTEP 5,000d								
Display	ICS4_9: LCD liquid crystal graphical display with backlighting     ICS689: Color TFT display 320 x 240 pixels     ICS4_9: Tactile-touch membrane keypad (PET), scratch-resistant material     ICS689: Piezo keypad scratch-resistant material								
Keypad									
Housing	Stainless steel 1.4301, AISI 304								
Protection	Up to IP69k								
Power	100-240 VAC; optional battery 12 V/2.5 A								
Standard Interfaces	1 RS232								

\*\*\* for digital platforms, the resolution is defined by the respective platform



5

Platform Size

QA 228 x 228 [mm]

A 240 x 300 [mm]

QB 305 x 305 [mm]

BB 300 x 400 [mm]

B 400 x 500 [mm]

BC 500 x 650 [mm] CC 600 x 800 [mm]

	PBD659	3 kg	
(in	Approved readability (6,000e)	0.5 g	
	Recommended readability at max. resolution (60,000d)	0.05 g	
	Ingress Protection	IP68/IP6	9k

PBA639	3 kg	6 kg	12 kg	15kg	30 kg	60 kg	120 kg	150 kg	300 kg	600 kg
Approved readability (3,000e)	1 g	2 g	n/a	5 g	10 g	20 g	n/a	50 g	100 g	200 g
Approved readability (2x3,000e)	n/a	1/2 g	n/a	2/5 g	5/10 g	10/20 g	n/a	20/50 g	50/100 g	100/200 g
Recommended readability at max. resolution (30,000d)	0.1 g	0.2 g	n/a	0.5 g	1 g	2 g	n/a	5 g	10 g	20 g
Ingress Protection	IP68/IP6	9k								



PBA439**	3 kg	6 kg	12 kg	15kg	30 kg	60 kg	120 kg	150 kg	300 kg	600 kg
Approved readability (3,000e)	1 g	2 g	n/a	5 g	10 g	20 g	n/a	50 g	100 g	200 g
Recommended readability at max. resolution (15,000d)	0.2	0.5	n/a	1	2	5	n/a	10	20	50
Ingress Protection	IP68/IP6	9k								

PBA436**	3 kg	6 kg	12 kg	15kg	30 kg	60 kg	120 kg	150 kg	300 kg	600 kg
Approved readability (3,000e)	1 g	2 g	n/a	5 g	10 g	20 g	n/a	50 g	100 g	200 g
Approved readability (2x3,000e)	n/a	1/2 g	n/a	2/5 g	5/10 g	10/20 g	n/a	20/50 g	50/100 g	100/200 g
Recommended readability at max. resolution (15,000d)	0.2	0.5	n/a	1	2	5	n/a	10	20	50
Ingress Protection	IP65									

\*3,000e / \*\*Only for ICS4x9 Combi Bench Scales

### High Precision, Bundle ICS Indicators with PBK989

PBK9 Series									
Platform Size (Load Plate Size)	0.6 kg	3 kg	6 kg	15 kg	30 kg	120 kg	150 kg	300 kg	600 kg
XS 210x250 (130x160 mm)	•								
A 275x345 (240x300 mm)		•	•						
AB 280x350 mm				•	•	•			
B 400 x 500 mm						•	•		
CC 600 x 800 mm							•	•	
Approved readability (30,000e)*	0.1 g	0.2 g	0.5 g	1 g	2 g	5 g	5 g	10 g	
Recommended readability at max. resolution (750,000d)*	0.005 g	0.01g	0.02 g	0.05 g	0.1g	0.2 g	0.2 g	0.5 g	
Ingress Protection	IP66/IP6	8							

\*max. readability/resolution, other resolutions see datashee

USB device/host, Ethernet, Digital I/O (4 Inputs + 4 Outputs)

ital IDNet, analog (max. 2 analog, or 2 IDNet resp. 1 analog + 1 IDNet) is accessories such as wall bracket, columns/stands, roller tops, printers, bator digital I/O, barcode scanners and much more

# Combine with the best fit platform for wet and harsh environments Modular Solutions, ICS429/439/449/469 and ICS689 Combi Bench Scales

12 kg	15kg	30 kg	60 kg	120 kg	150 kg	300 kg	600 kg
•	•						
•	•	•	•				
		•	•				
		•	•	•	•		
			•	•	•	•	
			•	•	•	•	•
					150 1.	000 1	000 L
12 kg	15kg	30 kg	60 kg	120 kg	150 kg	300 kg	600 kg

IZ NY	TONY	SU NY	OU KY	120 KY	150 Kg	300 KY	000 ky
2 g	n/a	5 g	10 g	20 g	n/a	50 g	200 g*
0.2 g	n/a	0.5 g	1 g	2 g	n/a	5 g	10 g

# **Compact Scales** For Hazardous Environments

The ICS4\_6x-Series combi bench scales are specifically designed for safe and accurate performance in potentially explosive environments. The scales are approved for use in hazardous areas classified as Zone 1/21 and Division 1. Select the right solution for your weighing application:

### **General specification Indicator**

Hazardous Area Approval	Zone 1/21, Division 1
Resolution for analog platforms	Up to OIML 2x3,000e/ NTEP 5,000d
Display	LCD liquid crystal graphical display with backlighting
Keypad	Tactile-touch membrane keypad (PET), scratch resistant material
Housing	Stainless steel 1.4301, AISI 304
Protection	IP65
Power	Either 120V or 230V via APS768x power supply
Standard Data Interface	Intrinsically safe RS232
Optional Data Interfaces	1 RS232 or RS422/485 via ACM200 communication module
Accessories	Choose from accessories such as wall bracket, columns/stands and printer (safe area)

### High Precision, ICS4\_6x Combi Bench Solution

	ICS426x: Basic Weighing ICS466x: Basic Weighing, Over/Under Checkweighing Over/Under, Filling/Dosing	
Attachable Platforms	1 digital weighing platform	

### High Precision, Bundle ICS4\_6x Indicators with PBK989

PBK9 Series		Capacity									
Platform Size (Load Plate Size)	0.6kg	3kg	6kg	15kg	30kg	60kg	120kg	150kg	300kg	600kg	
A 275x345 (240x300 mm)		•	•								
AB 280x350 mm				•	•	•					
Approved Readability*		0.1g	0.2g	0.5g	1g	2g					
Recommended Readability (min.)*		0.005g	0.01g	0.02g	0.05g	0.1g					

\*max. readability/resolution, other resolutions see datasheet

## Match the ICS466x to Your Requirements in Hazardous Areas

Applications	Basic Weighir				
Attachable Platforms	2 digital platfo				
Features	colorWeight <sup>®</sup> ,				

## Economic Solutions, ICS466x Combi Bench Scales

PBA439x								
Platform Size	3 kg	6 kg	15 kg	30 kg	60 kg	150 kg	300 kg	600 kg
QA 228 x 228 [mm]	•	•						
A 240 x 300 [mm]	•	•	•					
QB 305 x 305 [mm]			•	•	•			
BB 300 x 400 [mm]				•	•			
B 400 x 500 [mm]				•	•	•		
BC 500 x 650 [mm]					•	•	•	
CC 600 x 800 [mm]					•	•	•	•
Approved readability (3,000e)	1 g	2 g	5 g	10 g	20 g	50 g	100 g	200 g
Recommended readability at max. resolution (15,000d)	0.2	0.5	1	2	5	10	20	50
Ingress Protection	IP68/IP69	9k					•	

## Hygienic Design, ICS466x Combi Bench Scales

PBA639x								
Platform Size	3 kg	6 kg	15 kg	30 kg	60 kg	150 kg	300 kg	600 kg
QA 228 x 228 [mm]	•	•						
A 240 x 300 [mm]	•	•	•					
QB 305 x 305 [mm]			•	•	•			
BB 300 x 400 [mm]				•	•			
B 400 x 500 [mm]				•	•	•		
BC 500 x 650 [mm]					•	•	•	
CC 600 x 800 [mm]					•	•	•	•
Approved readability (3,000e)	1 g	2 g	5 g	10 g	20 g	50 g	100 g	200 g
Approved readability (2x3,000e)	n/a	1/2 g	2/5 g	5/10 g	10/20 g	20/50 g	50/100 g	100/200 g
Recommended readability at max. resolution (30,000d)	0.1 g	0.2 g	0.5 g	1 g	2 g	5 g	10 g	20 g
Ingress Protection	IP68/IP69	9k					•	

## High Precision, ICS466x Combi Bench Scales

PBK9 Series									
Platform Size (Load Plate Size)	3kg	6kg	15kg	30kg	60kg	120kg	150kg	300kg	600kg
A 275x345 (240x300 mm)	•	•							
AB 280x350 mm			•	•	•				
B 400 x 500 mm					•	•			
CC 600 x 800 mm							•	•	
Approved readability (30,000e)*	0.1 g	0.2 g	0.5 g	1 g	2 g	5 g	5 g	10 g	
Recommended readability at max. resolution (750,000d)*	0.005 g	0.01 g	0.02 g	0.05 g	0.1 g	0.2 g	0.2 g	0.5 g	
Ingress Protection	IP66/IP68	3	*		-				•

\*max. readability/resolution, other resolutions see datashee

18



ng, Over/Under CheckaweighinOver/Under, Filling/Dosing

orms or one analog and one digital platform

5 configurable soft keys, alphanumeric keypad

# **A Tailored Service Offering** Ensures Compliance and Reliability

From evaluating your needs to select the right scale, through to daily routine operation, our Sales & Service Team can accompany you every step of the way. The METTLER TOLEDO Good Weighing Practice approach GWP<sup>®</sup> ensures excellent performance, maximum uptime and full compliance with the norms and standards relevant to your industry.

#### **Evaluation and selection**

Our GWP<sup>®</sup> Recommendation service helps you select the right scale according to your specific process and quality requirements.

#### Installation

We document the installation and qualification of your scale in accordance with the relevant industry regulations. Operator training following installation leads to improved productivity.



#### Calibration

Scale calibration is at the core of accurate weighing results. Each calibration certificate declares the scale's minimum weight and measurement uncertainty.

#### **Routine operation**

GWP<sup>®</sup> Verification provides clear guidance for performance verification of your scale to save you time and money.

#### www.mt.com/gwp

www.mt.com/bench-scales .

For more information

METTLER TOLEDO Group Industrial Division Local contact: www.mt.com/contacts

Subject to technical changes ©03/2022 METTLER TOLEDO. All rights reserved Document No. 30234629 D MarCom Industrial