

# Industrial Basic Scales



## Industrial Basic Scales

Rugged Construction

Reliable Results

Affordable Solution



**Quality Scales**  
at Attractive Prices

**METTLER TOLEDO**

# Industrial Basics

## Quality Scales at Attractive Prices

**Industrial Basic Scales combine the manufacturing quality of METTLER TOLEDO with the simple and easy-to-use functionality of a production tool. These reliable and rugged scales are suitable for food, chemical or manufacturing applications. Check more products in a given time, count exactly, ensure completeness of packages and check whole pallets for their weight quickly. With Industrial Basic Scales, you can optimize your processes at an attractive price.**

### Basic Portioning Scales



#### Fast and Mobile Weighing

Get started with our basic rugged, reliable and easy-to-clean scales for weighing and portioning. You can choose the CUBII for wipe-down cleaning or opt for the ICS226 with a full stainless-steel construction. It features IP65/67 protection for light washdown applications in wet and humid environments.

### Durable Checkweighers



#### Weighing in Wet Environments

The BBA236 stainless-steel scale is a robust and easy-to-operate solution for many basic applications, such as portioning or checkweighing in partially wet environments. The user-friendly terminal, with its highly visible display, is fast and easy to operate.

### Hygienically Designed Bench Scale



#### Basic Weighing in Harsh Conditions

The BBA238 stainless-steel scale features a hermetically sealed load cell. It is robust and easy to operate. With a weighing capacity of up to 600 kilograms, it is ideal for many basic applications in wet and harsh industrial environments. It can communicate with a printer or PC through its built-in RS232 interface.

### Rugged Floor Scale



#### For Shipping and Receiving

The PFA220 is a fully electronic scale that delivers reliable weighing in rough environments. With its rugged construction, the floor scale provides accurate, repeatable weighing for a variety of industrial applications. Adjustable feet make it easy to level the scale on uneven floors.

Model	ICS226	CUBII	BBA236	BBA238	PFA220
Resolution OIML	3000e	3000e	3000e	3000d*	3000e**
Capacity Range	3 - 15kg	1.5 - 15kg	3 - 150kg	6 - 600kg	1500kg, 3000kg
Material	Stainless steel	Plastic	Stainless steel	Stainless steel	Painted steel
IP Terminal	IP67	IP65	IP66/IP67	IP66/IP67	IP54
IP Platform	IP65	IP65	IP65	IP68/69k	IP65

\*non approved resolution / \*\*CMC in China



### Simple Counting Scale



ICS241

#### Reliable, Fast and Accurate

The ICS241 is a basic counting scale for various industrial environments. Count metal, plastic and other parts for accurate order-picking, packaging and completeness checks. The ICS241 scale offers an easy-to-use interface, thanks to a large display and intuitive softkeys for direct access to key functions.

### Robust Bench Scale



BBA211

#### Simple Checkweighing

The BBA211 is designed for simple weighing and over/under checkweighing tasks. It provides up to 450 hours of battery life with mobile operation. Three different colored LED indicators provide easy-to-verify status indications. It comes with a non-approved readability up to 6'000d.

### Basic Industrial Bench Scale



BBA231

#### Basic Weighing in Harsh Conditions

The BBA231 bench scale is a robust and cost-effective solution for checkweighing applications in dry and dust-contaminated industrial environments, such as warehousing, production and shipping. The BBA231 designed for out-of-the-box straight weighing and comes with a non-approved readability up to 15'000d.

### Precise Pallet Weighing



PTA221

PTA226

#### Easy Warehousing


Basic pallet-weighing solutions offer reliability and flexibility for logistic and warehousing applications. The PTA scales are a cost-effective solution with an easily visible terminal display. The pallet scales are made out of mild-steel painted or stainless steel. The rugged design features integrated wheels for easy transportability.

Model	ICS241	BBA211	BBA231	PTA221	PTA226
Resolution OIML	3000e	3000e	3000e	3000e	3000e
Capacity Range	3 - 30kg	3 - 300kg	6 - 300kg	1500kg	1500kg
Material	Plastic	Painted steel	Powder-coated steel	Painted steel	Stainless steel
IP Terminal	IP43	IP65	IP54	IP54	IP66/67
IP Platform	IP43	IP65	IP65	IP67	IP68

\*non approved resolution

# Industrial Basics on the Web

► [www.mt.com/ind-basics](http://www.mt.com/ind-basics)



**Bench Scales and Portable Scales**  
Accurate and reliable weighing with industrial scales for a wide range of applications

How can we assist you?  
Document Finder  
Product Finder  
Service Finder  
eNewsletter  
VIP Zone

Overview Request Info Get a Quote

**Industrial Basics Scales**  
Industrial Basics scales feature quality scales at attractive prices. They are suitable for basic food, chemical or manufacturing applications in dry and wet environments.

- ★ **Rugged Construction**  
For long-lasting operation
- ★ **Reliable Results**  
For weighing and counting applications
- ★ **Affordable Solution**  
Optimize despite tight budgets

**Bench Scales**  
Compact bench scales offer highly accurate and precise weighing in industrial environments for weighing from 0.6 kg to 600 kg.

- ★ **Compact Scales**  
Wide weighing range for a variety of applications

**Counting Scales**  
Versatile counting scales for applications ranging from heavy duty industrial processes to laboratory analytics.

- ★ **Counting Scales**  
Count parts efficient and accurately

## METTLER TOLEDO Weighing Experience and Quality

With over 60 years of weighing expertise, METTLER TOLEDO is a leading global manufacturer of precision instruments. Our Industrial Basic Scales provide proven METTLER TOLEDO quality with stainless- or mild-steel weighing platforms, robust display foil and secure overload protection. Palette scales feature our unique shock absorbing Rocker-Foot technology. All scales are intensively quality tested and adhere to the required industry standards. Learn more about METTLER TOLEDO quality at:

► [www.mt.com/ind-basics](http://www.mt.com/ind-basics)

[www.mt.com/ind-basics](http://www.mt.com/ind-basics)

For more information

**Mettler-Toledo AG**  
Industrial Division  
CH-8606 Nänikon, Switzerland

Local contact: [www.mt.com/contacts](http://www.mt.com/contacts)

MTSI000000

