

Simplified Precision Weighing

Automotive Paint Mixing Scale





4 reasons to choose RPA345:



1. Boost Productivity with Simple Visibility

The simple, large graphic display with high resolution and enhanced contrast, enables operators to read weight information and prompts effortlessly, which makes the mix process easy to follow and reduces processing time and errors.





2. Achieve 100% Quality Formulations

The RPA345 has the ability to receive and manage formulas and jobs so that operators can execute the required processes efficiently. In case of an over pour, automatic recalculation enables the operator to adjust accordingly to complete an accurate batch and prevent waste.



3. Gain Efficiency with Flexible Connectivity

The standard USB or optional Bluetooth module allow operators to send a formula or job from a computer or mobile device to the scale, which eliminates cumbersome paper recipes and speeds up the time required to obtain the formula and start weighing.



4. Use One Scale for Any Operator

The easily adjustable screen enables ergonomic operation for users of any height, and duplicate buttons for zero and tare on each side of the indicator simplify use for right- and left-handed users and reduce the possibility of blocking the screen during the mix process.

RPA345 Refinish Scale Streamline Paint Mixing Processes


The RPA345 from METTLER TOLEDO is an economical, flexible paint mixing scale designed for the automotive refinish market. The high-resolution display, tilt-enabled screen and simple connectivity allow for more efficient and easy operation in the body shop. Built-in formulation software with guided steps simplifies processing and ensures high quality output every time. Let the RPA345 be your ideal paint-mixing assistant!

www.mt.com/ind-paint-mixing-scale

 2 | 3

Integrated Formula Management

5 Steps to Mix Your Paints



Send the formula to the scale

Formulas can be written into the scale via USB from a PC or via Bluetooth from a mobile device. The scale then provides clear guidance to the operators to ensure accurate, quality production.

Start mixing the formula

The formula and the target weights for each ingredient are displayed, and the scale prompts the operator to place the container onto the weighing platter, press tare, and begin the mixing process.

Mix each ingredient

Each ingredient will appear on the screen along with the target weight. When the amount poured is within tolerance, the scale prompts the operator to move to the next ingredient until the formula is complete.

Recalculate when necessary


A recalculation functionality is available when any ingredient has been under or over poured. Enabling over or under pour correction saves time and money by preventing bad batches and unnecessary waste.

Finish the mix

Once all ingredients are properly poured, the mixing data is automatically transmitted to your process management software. You can also manually send the information in case of any unexpected communication loss.



Built for convenience - Simplify scale maintenance



Protective covers for the display, column and weighing platter enable easy cleaning of the scale without risk of water ingress, protecting your investment.



Cable protection

The RPA345 is equipped with a hidden, routed channel that protects the power and communication cable from damage, making installation and daily use safe and hassle-free.

Technical Data

Metrological Data

Capacity	7,500 g / 999.95 g	
Readability	0.1 g / 0.05 g	
Tare range	-7,500 g	
Ambient temperature range	0 °C ~ 40 °C / 32 °F ~104 °F	
Power-on zero range	± 750 g	

Dimensions / Weight

Weighing platter	ø 234 mm	
Housing (W×D×H)	234 × 309 × 365 mm	
Scale net weight	Approx. 3.3 kg	

Display

Display / Keypad	Mono LCD graphic display / Membrane keypad	
Language	English, Chinese, Portuguese	

Power Supply

· · · · · · · · · · ·		
Power supply	USB 2.0 or higher, or AC adapter PSAI05R-050QL6	
Input voltage / Power consumption	5 VDC / 5 W	

Interface connectivity


USB or Bluetooth

Protection

IP protection	IP40 in accordance with EN 60529/IEC 60529	
Overvoltage degree	II	
Pollution degree		



Dimensional Drawings (mm)



Accessories

Order Number	Description	
Protective Covers		
30592535	Protective cover for display (pack of 10)	
30470151	Protective cover for column (pack of 10)	
30470152	Protective cover for platter (pack of 10)	
Power Supply		
30098591	USB Power adapter PSAI05R-050QL6	
46001774	AC-adapter plug (EU,BR)	
46001775	AC-adapter plug (AU)	
46001776	AC-adapter plug (US, CN)	
46001777	AC-adapter plug (UK)	
Cables		
30592533	USB Power & Data Cable, RJ45 to USB, 3m	
30592534	Bluetooth Power & Data Cable, RJ45 to USB, 3m	
Weighing Platter		
30570797	Weighing platter RPA455	

6

Built-In Bluetooth® Module

Simple Installation and Formula Transmission

The RPA345's integrated Bluetooth module allows the operator to push a formula or job instructions from a mobile phone directly to the scale, eliminating manual processing time and delivering step-by-step operator guidance to ensure error-free mixing.

When the scale is connected with a Bluetooth cable, its Bluetooth ID will be shown on the display to help you quick pair with your device.



www.mt.com/ind-paint-mixing-scale

For more information





Industrial Division Local contact: www.mt.com/contacts



Subject to technical changes @08/2021 METTLER TOLEDO. All rights reserved Document No. 30592510 A MarCom Industrial

