



Capacity	Location and dimensions (mm [inch])						
	L1	L2	L3	L4	L5	L6	D1
1T / 3T	140 [5.51]	110 [4.33]	12 [0.47]	27 [1.06]	12 [0.47]	83 [3.26]	11.2 [0.44]
10T / 30T	210 [8.26]	160 [6.29]	19 [0.74]	34 [1.33]	15 [0.59]	102.6 [4.03]	22 [0.86]



RoHS/REACH conform

Length	0.5...3	>3...6	>6...30	>30...120	>120...400	>400	Angle	>0...10	>10...50	>50...120	>120...400	R+Chamfer	0.5...3	>3...6	>6
medium	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8	medium	±1°	±0°30'	±0°20'	±0°10'	medium	±0.2	±0.5	±1

Material: -						Standard threads: ISO: 6H / 6g ANSI: class 2					
Material2: -						Size ISO 14405					
Finish: -						General geometrical tolerances ISO 2768-K					
All Dimensions are finished dimensions post surface treatment											
METTLER TOLEDO											
Title						Refer to protection notice ISO 16016					
SLL210 Plate Kit						ERP Number 30966580 ERP Revision					
Design						Status Released					
Rev B						Units MM 1/1					

B	A5	Add dimension L5	Bingzheng	Ermanuel			2026.10	
A			Binbin	Bingzheng			2024.06	
REV / CHG	ZONE	DESCRIPTION	BY	APPVD	AGENCY	E.R. NO.	DATE	

RECORD OF CHANGES