## **Application Versatility**

# For General-Purpose Transaction Weighing



#### Multiple applications

For maximum flexibility, the terminal adds five selectable transaction weighing applications to its simple weighing capability. A vivid graphic display, easy set-up and intuitive on-screen prompting increase productivity through reduced operator training.



#### **Power options**

Choose from universal AC power or battery version. The long-life externally chargeable NiMH battery provides ultimate portability. The compact battery can power the system for up to 30 hours between charges. An external charger is required.



#### **Utilities**

User-friendly utilities include print templates with customizable text strings, report view and print, maintenance diagnostics and statistics, password protection and a PC-based file transfer tool.



#### Connectivity

Two available option slots enable a broad range of connectivity interfaces. Use serial, USB or Ethernet connections to exchange application transaction data and ID files using the PC-based file transfer tool.



## ND246 Terminal

Productivity by Design

For simple weighing or for specific basic level applications like over/under checkweighing, inbound/outbound vehicle weighing, peak weight measurement, animal weighing and counting, this terminal provides best-inclass flexibility, performance and operator interface. The terminal includes a large backlit graphic LCD display, an operator-friendly keypad layout with function, alphanumeric and navigation keys, support for SD memory card and application-specific print templates. These characteristics make it the most versatile general purpose transaction weighing terminal available.

- 100 240 VAC power, or NiMH battery model
- Alphanumeric keypad for quick entry of tare and ID information
- Large, back-lit graphic LCD display, readable under varying light conditions
- Automatic shutoff and backlight timeout features help extend battery life
- Isolated COM1 and optional COM2 ports
- Control of external devices using Discrete I/O
- PC-based File Transfer Tool (FTT) to exchange ID and target tables between terminal and PC



### **IND246**

## Application Versatility Meets Operator Productivity

#### **Application Pacs**

- Five applications ready for use:
  - Animal Weighing: Generates average weight for one animal, or average weight-per-animal for multiples
  - ◆ Counting: Prompts operator through piece counting sequence to help reduce operator errors. Includes accumulation by part ID
  - Checkweighing: Over/Under operation with clear on-screen status display, can control status lights
  - Peak Weight Measurement: Displays the peak weight from the current weighing cycle, or maximum, minimum and average peak weight from a multi-sample weighing cycle
  - ♦ Vehicle Weighing: Permanent or Temporary ID weighing for one- and two-pass operation



## Technical Data

Dimensions (WxHxD)	Without bracket: 230 x 146 x 165 mm / 9" x 5.75" x 6.5" With bracket: 230 x 165 x 195 / 9" x 6.5" x 7.7"			
Construction	Stainless Steel			
Power	AC: 100 - 240 VAC			
	Battery: NiMH, removable, externally charged. 1 load cell - 25 hours; 4 load cells - 20 hours. External charger optional			
Mounting	Fixed-position bracket included			
Operating Environment	-10°C to +40°C (14°F to 104°F), 10% to 95% relative humidity, non-condensing			
Protection	IP66			
Display	Transflective backlit graphic LCD, 240 x 96 pixels Weight display: Standard mode, 1.1"/27 mm high. Application mode, 0.8"/20 mm high			
Scale Interface	Analog load cell			
Units of Measure	g, kg, lb, oz, t, ton			
Load Cells	AC version Battery version		load cells, 10V Excitation oad cells, 5V Excitation	
Keypad	8 function keys, 4 navigation keys, 12-key alphanumeric keypad, On/Off button			
Memory	Battery-backed internal			
Applications	Animal Weighing	User-defined sampling period; 1-9.9 seconds. ID input and display Display modes for average total weight and average weight-per-animal for single or multiple animals		
	Counting	Two counting sequences: Tare-Sample (APW) and Sample-Tare; accumulation by part ID		
	Checkweighing	3 Zones, up to 25 targets; SmartTrac® graphical representation — small or large		
	Peak Weight	Single or multi-cycle mode selection. Multi-cycle mode shows maximum, minimum and average peak weight; Control of external devices via optional discrete I/O; Memory report view and print		
	Vehicle Weighing	Storage of 99 permanent tares and 99 temporary tares by ID; Auto-assignment of ID; totalization by Permanent ID; 4,000 stored transactions		
Communication Options	Standard	COM1	RS-232, isolated	
	Option Slot 1	COM2	RS-232/485, isolated	
		COM2 + D I/O	RS-232/485, isolated + 2 inputs and 4 outputs	
		USB	Device type*	
		USB + D I/O	Device type* + 2 inputs and 4 outputs	
			* Only for connection to PC	
	Option Slot 2	Ethernet TCP/IP,	10/100 Base-T	
Approvals	Weights & Measures	OIML: Class III 6000e, Class IIII 1000e, R76/2006-NL1-11.12 Europe: Class III 6000e, Class IIII 1000e, TC7918 USA: NTEP III, IIIL – 10,000d/2x5000d; CoC 11-040; Canada: III, IIIHD - n max 10,000/20,000; AM-5819		
	Product Safety	UL, cUL, CE		

## Accessories

Tilt/Swivel Bracket NiMH Battery Pack Battery Pack Charger



Mettler-Toledo, LLC 1900 Polaris Parkway Columbus, OH 43240 Phone 800 438 4511 Fax 614 438 4900

Subject to technical changes © 04/2014 Mettler-Toledo, LLC INDB0084.EN.03 A4 www.mt.com/IND246 \_

For more information